

自動撕膜機

csun

Auto Mylar Peeler

MP-A25T



機台特點 Key Features

潔淨作業 Clean Operation

作業流程不吹氣，避免膜屑飛散

Air-free process prevents film debris from becoming airborne.

FFU + HEPA 潔淨氣流由上往下，降低揚塵

FFU + HEPA provides downward clean airflow to minimize airborne particles.

分膜穩定 Stable Film Separation

前緣整列輾壓，位置、壓力及次數皆可依需求設定

Front-edge roller pressing with adjustable position, pressure, and number of passes.

撕膜穩定 Stable Film Peeling

膠帶起膜，每次使用全新膠帶區段，確保黏性穩定

A fresh section of tape is used for each film pickup, ensuring consistent adhesion.

具起膜檢知功能；起膜失敗時可重新執行，降低撕膜失敗率

Film pickup detection allows automatic retry upon failure, reducing peeling errors.



www.csun.com.tw

Leading in Thermal and UV Light Processing Equipment

MP-A25T

機台尺寸 Machine Size	L1920 × W1450 × H2372 mm
入料高度 Pass Line	950 ± 50 mm
基板尺寸 Panel Size	寬 510 mm 長 510–610 mm 厚 0.2–3.2 mm
撕膜系統 Peeling System	前留銅 Bare Leading Edge: 1–5 mm 撕膜方式 Film Peeling Method: 輾壓分膜 → 膠帶起膜 → 夾爪撕膜 Roller Separation → Tape-Assisted Film Pickup → Gripper Peeling
進料段 Infeed Section	小型化設計，需另外搭配自動放板機中央整板供料進行撕膜。 Compact design. An auto loader with a centering device is required for panel feeding.
出料段 Outfeed Section	向後推移，方便維修與更換耗材。 Retractable design for easy maintenance and consumable replacement.
Mylar 回收 Mylar Collection	回收桶收集 Collected in a recycling bin.
異常暫存功能 NG Buffer	4 pcs
控制方式 Operation Control	可程式控制器 + 觸控式螢幕 PLC + Touch Panel
外部供應 Utilities	電力 Power: AC 220 V, 3φ, 50/60 Hz, 3 kVA, 6 A 氣源 CDA: 7 kg/cm ² , 100 L/min

Due to C SUN continuing efforts to improve their systems, these specifications are subject to change without notice.
受長期研發需要，本公司保有規格修改之權利，恕不另行通知

DM2026Q4

sale@csun.com.tw

台北

新北市林口區工二工業區
工八路2-1號
TEL: 886-2-26017706
FAX: 886-2-26018854

台中

台中市南屯區
精科二路11號
TEL: 886-4-23591651
FAX: 886-4-23592678

廣州

廣州市花都區獅嶺鎮
利和路6號
TEL: 86-20-86846341-3
FAX: 86-20-86910139

東莞

東莞市大朗鎮長塘第三工業區78號
松湖雲谷雲松樓1樓
TEL: 86-769-85331146
FAX: 86-769-85331145

昆山

江蘇省昆山市高新區(玉山鎮)
恒盛路1369號
TEL: 86-512-57780230
FAX: 86-512-57780229