# Vacuum pumps / EJ-BSVLG

# **EJ-BSVLG-LARGE-ISO**

- Ideal for centralized and decentralized applications
- Excellent ratio between suction flow rate and compressed air consumption
- Available with ON/OFF vacuum valve, blow-off, and integrated manual override control
- POM manifold prepared for mounting ISO 15407-1 (18 mm) valve of type 2x 3/2 NC or 5/3 with closed centre
- Available with two- and three-stage EJ-LARGE cartridges (EJ-HF and EJ-HV)
- Additional vacuum ports for mounting a vacuum switch
  In-line design for greater dirt tolerance
- Installable in series


## **Typical applications**

- Case packing and cartoning machines
- In applications that require an integrated control system with reduced weight and compact dimensions (electronics sector)
- Handling objects with heavy weights and porous surfaces

NEW



### Application example






Pump technical features					
Max feed pressure	0.7 MPa				
Weight (with solenoid valve)	260 (450) g				
Material	SS, POM, AI, Nitrile (NBR)				
Noise level	< 70 dB				
Operating temperature	-5 ÷ +50 °C				


Solenoid valve technical features (optional)						
Brand	Festo					
Model	VSVA-B-T32C-AZH-A2-1R5L					
Operation	2x 3/2 Normally closed (NC), spring loaded A					
Type of electrical connection	M12x1 4-pin					
Drive voltage	24 Vcc ±10%					
Power absorption	1/2.4 W (min/max)					
IP rating	IP65					
Piloting	External					
Standard	ISO 15407-1: VDMA 24 563					

Features of compatible valves						
tandard ISO 15407-1 (18 mm)						
Required piloting	External					
Operation	2x 3/2 NC	A	5/3 CC	В		
Piloting outlet	Not conveyed					

Example of compatible valves						
Brand	Coding	Lay-out				
Aignep	05V S0 7 CC 00	В				
Festo	VSVA-B-T32C-AZH-A2-1C1	Α				
Festo	VSVA-B-T32C-AZH-A2-1R5L	Α				
Festo	VSVA-B-P53C-ZH-A2-1C1	В				
Norgren	V415A22D-C313A	A				

В





Suction flow rate													
Model	Feed pressure	Air consumption		Suction flow rate [NI/s] at different vacuum levels [kPa]					Max vacuum				
	[MPa]	[NI/s]	0	-10	-20	-30	-40	-50	-60	-70	-80	-90	[kPa]
EJ-BSVLG-L-HF-2-ISO	0.6	1.7	3.2	3.0	2.5	1.7	0.89	0.62	0.51	0.31	_	_	-73
EJ-BSVLG-L-HF-3-ISO	0.6	1.7	5.9	3.5	2.5	1.7	0.89	0.62	0.51	0.31	_	_	-73
EJ-BSVLG-L-HV-2-ISO	0.5	1.93	2.6	2.4	1.7	1.3	0.70	0.55	0.40	0.31	0.15	0.02	-94
EJ-BSVLG-L-HV-3-ISO	0.5	1.93	6.0	3.7	2.1	1.9	0.79	0.55	0.40	0.31	0.15	0.02	-94


For technical specifications, regarding the suction flow rate and the air consumption at different pressures, please refer to the technical data sheets of the EJ-LARGE cartridges in the two- and three-stage versions

Evacuation time												
Model	Feed pressure	Air consumption		Evacuation time [s/I] to reach different vacuum levels [kPa]					Max vacuum			
	[MPa]	[NI/s]	-10	-20	-30	-40	-50	-60	-70	-80	-90	[kPa]
EJ-BSVLG-L-HF-2-ISO	0.6	1.7	0.03	0.07	0.12	0.19	0.3	0.4	0.7	-	-	-73
EJ-BSVLG-L-HF-3-ISO	0.6	1.7	0.02	0.05	0.10	0.19	0.3	0.4	0.7	_	_	-73
EJ-BSVLG-L-HV-2-ISO	0.5	1.93	0.04	0.09	0.16	0.3	0.4	0.6	0.9	1.3	2.5	-94
EJ-BSVLG-L-HV-3-ISO	0.5	1.93	0.02	0.06	0.10	0.2	0.3	0.4	0.7	1.1	2.4	-94

For technical specifications regarding the evacuation time and the consumption at different pressures, please refer to the technical data sheets of the EJ-LARGE cartridges, in the two- and three-stage versions



Identification codes		
Alphanumeric code	Description	Order code
EJ-BSVLG-L-HF-2-ISO	$\hbox{EJ-BSVLG-LARGE-HF-2-ISO vacuum pump with holder and integrated silencer, ready for ISO~15407-1~valve,} \\ G1/2" vacuum port$	3030219
EJ-BSVLG-L-HF-3-ISO	EJ-BSVLG-LARGE-HF-3-ISO vacuum pump with holder and integrated silencer, ready for ISO 15407-1 valve, G1/2" vacuum port	3030220
EJ-BSVLG-L-HV-2-ISO	EJ-BSVLG-LARGE-HV-2-ISO vacuum pump with holder and integrated silencer, ready for ISO 15407-1 valve, $G1/2$ " vacuum port	3030221
EJ-BSVLG-L-HV-3-ISO	EJ-BSVLG-LARGE-HV-3-ISO vacuum pump with holder and integrated silencer, ready for ISO 15407-1 valve, G1/2" vacuum port	3030222
EJ-BSVLG-L-HF-2-ISO-NC-M12	EJ-BSVLG-LARGE-HF-2-ISO vacuum pump with holder and integrated silencer, with $3/2$ x2 NC solenoid valve for vacuum and blow-off, M12x1 4-pin connection, G1/2" vacuum port	3030227
EJ-BSVLG-L-HF-3-ISO-NC-M12	EJ-BSVLG-LARGE-HF-3-ISO vacuum pump with holder and integrated silencer, with $3/2$ x2 NC solenoid valve for vacuum and blow-off, M12x1 4-pin connection, G1/2" vacuum port	3030228
EJ-BSVLG-L-HV-2-ISO-NC-M12	EJ-BSVLG-LARGE-HV-2-ISO vacuum pump with holder and integrated silencer, with $3/2$ x2 NC solenoid valve for vacuum and blow-off, M12x1 4-pin connection, G1/2" vacuum port	3030229
EJ-BSVLG-L-HV-3-ISO-NC-M12	EJ-BSVLG-LARGE-HV-3-ISO vacuum pump with holder and integrated silencer, with $3/2$ x2 NC solenoid valve for vacuum and blow-off, M12x1 4-pin connection, G1/2" vacuum port	3030230



Notes		